


END EFFECTORS



HIWIN Support



About HIWIN

Electric Gripper XEG Series



XEG-32

Features

- Integrated with stepper motor and encoder featuring status feedback, abnormal alarm, object identification and signal output.
- Using linear module to achieve high speed, high precision, high rigidity, high efficiency and advantage of compact size.
- Equipped with auto-reset and gripping force adjustment for smart function like real-time adaptive capture.
- Direction, stroke, force, speed etc. can be set, and the software has the function of using the recorded history.
- Supports both serial and I/O communications, providing flexibility and convenience to users.

Model		XEG-32
Total Stroke (mm)		32
Gripping Force (N)		60~150
Speed (mm/s)	Moving	1~80
	Gripping	1~20
Repeatability (mm)		±0.01
Weight (kg)		0.7
IP Class		IP20
Cleanroom Class		ISO Class 5 (Class 100)

* Note 1: The weight of workpiece(kg) acceleration of gravity $9.81(\text{m/s}^2)$ should be $1/10 \sim 1/20$ of the gripping force(N). If the gripper holding a workpiece moves or turns with high-acceleration/deceleration, choose the model with higher force allowance.

* Note 2: To find out more details for the projects of "TM Robotics Plug & Play" and "UR+ Robotics Solutions", please visit HIWIN official website.

Electric Gripper XEG Series



XEG-64

Features

- Integrated with stepper motor and encoder featuring status feedback, abnormal alarm, object identification and signal output.
- Using linear module to achieve high speed, high precision, high rigidity, high efficiency and advantage of compact size.
- Equipped with auto-reset and gripping force adjustment for smart function like real-time adaptive capture.
- Direction, stroke, force, speed etc. can be set, and the software has the function of using the recorded history.
- Supports both serial and I/O communications, providing flexibility and convenience to users.

Model		XEG-64
Total Stroke (mm)		64
Gripping Force (N)		180~450
Speed (mm/s)	Moving	1~100
	Gripping	1~20
Repeatability (mm)		±0.01
Weight (kg)		1.9
IP Class		IP20
Cleanroom Class		ISO Class 5 (Class 100)

* Note 1: The weight of workpiece(kg) acceleration of gravity $9.81(\text{m/s}^2)$ should be $1/10 \sim 1/20$ of the gripping force(N). If the gripper holding a workpiece moves or turns with high-acceleration/deceleration, choose the model with higher force allowance.

* Note 2: To find out more details for the projects of "TM Robotics Plug & Play" and "UR+ Robotics Solutions", please visit HIWIN official website.

Electric Gripper Controller XEG Series



XEG-C1



XEG-C2



Model		XEG-C1
Voltage (V)		DC24±10%
Current (A)		0.5
External I/O	Input	5 points: Command point setting 1 point: Command input
	Output	6 point: motion output
Serial Communication		RS232(USB)
Number of Points	External I/O	30+1 set (Include original reset)
	Serial Communication	Unlimited
IP		20
Weight (kg)		0.15
Safety Circuit		N/A
ID Setting		N/A
Terminal Resistor		N/A

Model		XEG-C2
Voltage (V)		DC24±10%
Current (A)		0.5
External I/O	Input	6 points: Command point setting 1 point: Command input 1 point: Firmware version update
	Output	8 point: motion output
Serial Communication		RS485(Modbus-RTU)
Number of Points	External I/O	62+1 set (Include original reset)
	Serial Communication	Unlimited
IP		20
Weight (kg)		0.3
Safety Circuit		Trigger emergency stop (Servo OFF)
ID Setting		Rotary DIP switch (0-F), 15 stations
Terminal Resistor		120Ω

Integrated Electric Gripper SEG Series



SEG-24

Features

- Integrated control system
The controller is embedded inside the gripper and the system has built-in motion parameters.
- User friendly
Users control I / O signals easily, no need to edit programs and parameters.
- SEG-24
Press to set up high-efficiency grip mode on gripper panel, with instant adaptive grip, mode adjustment and other intelligent function.

Model			SEG-24
Gripper Spec.	Stroke Per Side (mm)		12
	Gripping Force (N)		35
	Speed (mm/s)	Moving	45
		Gripping	15
	Repeatability (mm)		±0.1
	Weight (kg)		0.7
	Voltage (V)		24
	Current (A)		0.5
	IP		20

* Note 1: The weight of workpiece(kg) acceleration of gravity 9.81(m/s²) should be 1/10~1/20 of the gripping force(N).If the gripper holding a workpiece moves or turns with high-acceleration/deceleration, choose the model with higher force allowance.

* Note 2: To find out more details for the projects of "TM Robotics Plug & Play" and "UR+ Robotics Solutions", please visit HIWIN official website.

Global Sales and Customer Service Site

HIWIN GmbH

OFFENBURG, GERMANY
www.hiwin.de
www.hiwin.eu
info@hiwin.de

HIWIN USA

CHICAGO, U.S.A.
www.hiwin.com
info@hiwin.com

HIWIN JAPAN

KOBE • NAGOYA • TOKYO • TOHOKU •
NAGANO • SHIZUOKA • HOKURIKU •
HIROSHIMA • FUKUOKA • KUMAMOTO,
JAPAN
www.hiwin.co.jp
info@hiwin.co.jp

HIWIN Srl

BRUGHERIO, ITALY
www.hiwin.it
info@hiwin.it

HIWIN Schweiz GmbH

JONA, SWITZERLAND
www.hiwin.ch
info@hiwin.ch

HIWIN s.r.o.

BRNO, CZECH REPUBLIC
www.hiwin.cz
info@hiwin.cz

HIWIN FRANCE

STRASBOURG, FRANCE
www.hiwin.fr
info@hiwin.de

HIWIN SINGAPORE

SINGAPORE
www.hiwin.sg
info@hiwin.sg

HIWIN KOREA

SUWON • CHANGWON, KOREA
www.hiwin.kr
info@hiwin.kr

HIWIN CHINA

SUZHOU, CHINA
www.hiwin.cn
info@hiwin.cn

HIWIN BULGARIA

SOFIA, BULGARIEN
www.hiwin.bg
info@hiwin.bg

HIWIN®

HIWIN TECHNOLOGIES CORP.

No. 7, Jingke Road,
Taichung Precision Machinery Park,
Taichung 408208, Taiwan
Tel: +886-4-23594510
Fax: +886-4-23594420
www.hiwin.tw
www.hiwinsupport.com
business@hiwin.tw (Sales)
robotservice@hiwin.tw (Customer Service)

- HIWIN is a registered trademark of HIWIN Technologies Corp.. For your protection, avoid buying counterfeit products from unknown sources.
- Actual products may differ from specifications and photos provided in this catalog. These differences may be the result of various factors including product improvements.
- HIWIN website for patented product directory: http://www.hiwin.tw/Products/Products_patents.aspx
- HIWIN will not sell or export products or processes restricted under the "Foreign Trade Act" or related regulations. Export of restricted products should be approved by proper authorities in accordance with relevant laws and shall not be used to manufacture or develop nuclear, biochemical, missiles or other weapons.

The specifications in this catalog are subject to change without notification.

Copyright © HIWIN Technologies Corp.

©2023 FORM C98DE05-2304 (PRINTED IN TAIWAN)